

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Россия (495)268-04-70

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Казахстан (772)734-952-31

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

<https://biobase.nt-rt.ru/> || bba@nt-rt.ru

Процессоры автоматизированные BK-TS2



Features

- * Imported high-quality parts, smooth operation, low noise, ergonomic design
- * Intelligent automatic water influx/efflux/drainage control system
- * Green inner-cycling air purification system remove poisonous gas(BK-TS2)
- * 4 sets of editable programs can be queried on line(BK-TS2)
- * Real-time visual simulation with icons displays working status dynamically, clearly and intuitively(BK-TS2)
- * Small footprint can be placed near the sectioning area for optimal workflow (BK-TS3)
- * The APS-coated sturdy housing, resistance to corrosion
- * The slide rack can be optionally stopped either above or submerged in cup based on user's selection after the staining process ends
- * Operation error alarm

Technical Parameters

Model BK-TS2

Display LCD touch screen

Cup Number 18 (Station 1 is for drying, Station 10 is for washing)

Single Cup Capacity 750ml

Each Cup Processing Time 0~59 min

Slides Processed Simultaneously 52 slides

Dripping Time Adjustable within 0~30 s (shakes above cup)

Consumption 500W

Power Supply AC220V±10%, 50/60Hz; AC110V±10% 60Hz

Packing Size(W*D*H) 1175×460×470 (mm)

Gross Weight 71KGS